

precision pointers

MAHR 1010 precision pointer Millimess



Application:

For measuring lengths. Ideal for measuring instruments and flatness and straightness measurements

Version:

- Impact-resistant
- Ball-guided measuring pin
- Connection for wire lifter
- Pointer fine adjustment
- Adjustable tolerance marks



Art. no.	33163 110
Scale value	0.01 mm
Length measuring range	0.5 mm
Shaft diameter	8 mm
Shaft length	20 mm
Error limit	8 µm
With free stroke	Yes
Measurement force	1 N
Repeat accuracy	2 µm
Calibration Group	K
DIN	879

EAN-Code

4059 1920 14025