



TH-3 Relative Humidity Temperature Meter

- Dual display
- Relative function monitors humidity and temperature changes
- Extended probe stem to easily access air ducts
- Min/Max readings
- Data Hold
- Capacitive sensor with protective cover
- Auto Power off
- Soft Carrying Case
- One-year warranty

No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: €500 MSLP limit)

The TH-3 uses a precision capacitance sensor to deliver accurate performance with long term stability. This high accuracy instrument measures the full range of relative humidity from 0% to 100% and features an exceptionally wide ambient temperature measurement range from -20 °C (-4 °F) to 60 °C (140 °F). The sensor is mounted on a long shaft extending from the top surface of the unit, making probing into ductwork and hard to reach areas more easy. The large LCD displays two measurements simultaneously with a full range of display options including Hold, Min, Max, and Relative. The TH-3 is a complete package and comes with soft carrying case, sensor cover, battery and manual.

Included Accessories

Soft carrying case, sensor cover, battery (installed), users manual

General Specifications

Display	Dual display
Operating Conditions:	0 °C to 40 °C
Storage Conditions:	-10 °C to 60 °C; <70 % RH
Altitude	Up to 2000 meters
Sample rate	2.5 times per second
Battery	9 V Battery, NEDA 1604 or JIS 006P or IEC6F22
Battery life	85-hours continuous (with alkaline battery)
Dimension	240 x 54 x 34 mm (9.5 x 2.1 x 1.3 in.)
Weight	Approximately 180 g (6.4 oz.)

Technical Specifications

Function	Range	Accuracy
Measurement Ranges		
Humidity	0 % RH to 100 % RH	
Range accuracy	5 % RH to 95 % RH: <5%RH, >95% RH	±3 % RH @ 23 °C ±5 % RH @ 23 °C
Temperature Coefficient:		0.1 x specified accuracy/ °C <23 °C, >23 °C
Resolution	0.1 %RH	
Temperature (Dry Bulb)	-20 °C to 60 °C: -4 °F to -140 °F	±0.8 °C ±1.6 °F
Resolution	0.1 °C/0.1 °F	
Response time (in slowly moving air)		
Humidity	180 sec	
Temperature	10 sec	

Amprobe® Test Tools
 website: www.Amprobe.com
 email: info@amprobe.com
 Everett, WA 98203
 Tel: 877-AMPROBE

Beha-Amprobe GmbH
 In den Engematten 14
 79286 Glottertal, Germany
 Tel.: +49 (0) 7684 8009 - 0
info@amprobe.eu