




VDOGQ090PLS0003E03STGF040MSS

Connection technology



Product characteristics

Parameter setting cable for efector octavis

M8 plug / Sub D socket

Electrical data

Electrical design

AC/DC

Operating voltage [V]

60 AC / 75 DC

Protection class

III

Environment

Ambient temperature [°C]

-25...85

Protection

IP 50

Mechanical data

Design

straight / straight

Material body

PUR

Material nut

Brass; nickel-plated

Weight [kg]

0.112

Electrical connection



Connection

PVC cable / 3 m;
3 x 0.25 mm² (32 x Ø 0.1 mm); Ø 5 mm


Sheath colour

black

Wiring



5 4 3 2 1



Remarks

Pack quantity [piece]

1