



AS-INTERFACE COMPACT MODULE K60, IP67, A/B-SLAVE (SPEC. 3.0), ANALOG, 2AI(1AI), 2(1)X INPUT CURRENT 4..20MA; +/-20MA; M12-SOCKETS. RESOLUTION 12 /14BIT, 1- OR 2-CHANNEL OPERATION, CHANGEOVER THROUGH ID1-CODE. MOUNTING PLATE 3RK19010CA00 TO BE ORDERED SEPARATELY.

General technical data:

Design of the product		analog I/O modules for operation in the field, IP67 - K60
Type of device		analog input modules for current measurement
Type		2 inputs
Design of the slave type		A/B analog slave (Spec. 30)
I/O configuration		7
ID code		A
Type of electrical connection of the inputs and outputs		M12 screw-type terminals
Total current Input when connected from sensors/actuators	mA	150
operating voltage according to AS-Interface specification	V	26.5 ... 31.6
Current consumption when connected		
• 2 sensors		
— without Uaux infeed max	mA	46
— from Uaux infeed max.	mA	500
Voltage supply auxiliary voltage additional for sensors Uaux	V	24 ... 30
Profile		7.A.9
Measuring/output value		current
Measuring/output range		adjustable: 4 ... 20 mA / +/-20 mA
Smoothing function		configurable
Channels active		1 and 2
A/D resolution for analog inputs/outputs	bit	14

Type of connection		4-conductor
--------------------	--	-------------

Inputs:

Number of analog inputs		2
Inputs sensors		2/3/4-conductor sensors
Input variable		mA
Product function input variable parameterizable		Yes
Number of analog outputs		0
Output quantity		
• Current signal		Yes
Status display		
• AUX PWR (Uaux)		green LED
• AS-Interface		green LED
• FAULT		red LED

Ambient conditions:

Ambient temperature		
• during operation	°C	-20 ... +60
• during storage	°C	-40 ... +85
Protection class IP		IP67

Mechanical data:

Width	mm	60
Height	mm	152
Depth	mm	29
Mounting type		standard rail mounting/wall mounting using mounting plate for K60 compact module

Certificates/ approvals:

Approvals		UL, CSA, shipbuilding available soon
-----------	--	--------------------------------------

General Product Approval



CSA



GOST



UL



ABS



BUREAU
VERITAS

Shipping Approval



DNV



LRS



PRS



RMRS

other

[Environmental
Confirmations](#)

[Declaration of
Conformity](#)

other

[Confirmation](#)

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK22071BQ500AA3>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RK22071BQ500AA3/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK22071BQ500AA3&lang=en>





last modified:

09.03.2015