


TECHNICAL SPECIFICATIONS

Material: Zinc, Nickel Plated
Operating Temperature: -40°C to +120°C
Cable Entry: Side Entry
Cable O.D: Up to 13mm
Accessories: See page 186-190
Assembly Instruction: See page 197



Features:

- Full Metal Slide-Lock System Hood
- Available in sizes 9-15-25-37
- Excellent EMI Shielding
- Re-openable
- Strain relief inserts ensure a secure termination
- Metalized (RAHI) grommets on request - See page 186



Grommet Sizes - MHDVSL09-37:

Size MHDVSL	Dim A	Dim B	Dim C
9-way	14,5	36,3	31,0
15-way	14,5	40,3	39,5
25-way	14,5	40,3	53,2
37-way	14,5	40,3	69,7

Ordering information:

Size:	P/N - Kitted:	Product Code:
9-way	6560-0206-31	MHDVSL-09-K
15-way	6560-0206-32	MHDVSL-15-K
25-way	6560-0206-33	MHDVSL-25-K
37-way	6560-0206-34	MHDVSL-37-K

Size:	P/N - BULK:	Product Code:
9-way	6561-0206-31	MHDVSL-09
15-way	6561-0206-32	MHDVSL-15
25-way	6561-0206-33	MHDVSL-25
37-way	6561-0206-34	MHDVSL-37