

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1716920206](#)  
**Status:** **Active**  
**Overview:** Mega-Fit Power Connectors  
**Description:** Mega-Fit TPA-Capable Receptacle Housing, Dual Row, 6 Circuit, UL 94V-0, Glow-Wire Capable, Black

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Product Specification 1054171000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 1716920200-000 \(PDF\)](#)

**General**

Product Family Crimp Housings  
Series [171692](#)  
Application Power, Wire-to-Board, Wire-to-Wire  
Datasheet Order No 987650-5401  
Overview [Mega-Fit Power Connectors](#)  
Product Name Mega-Fit  
UPC 191130070602


**Physical**

Circuits (maximum) 6  
Color - Resin Black  
Gender Receptacle  
Glow-Wire Capable Yes  
Keying to Mating Part None  
Lock to Mating Part Yes  
Material - Resin Nylon  
Net Weight 3.430/g  
Number of Rows 2  
Packaging Type Bag  
Panel Mount No  
Pitch - Mating Interface 5.70mm  
Pitch - Termination Interface 5.70mm  
Polarized to Mating Part Yes  
Stackable No  
Temperature Range - Operating -40° to +105°C, -40° to +120°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification 1716920200-000  
Product Specification 1054171000-PS-000  
Sales Drawing 1716920200-000



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[171692](#) Series

**Mates With**

Mega-Fit Headers [76825](#) , [76829](#) , [172065](#) ,  
[172064](#) <br>Mega-Fit Plug Housing [105411](#)

**Use With**

Mega-Fit TPA [105415](#) <br>Mega-Fit Crimp  
Terminals [76823](#) , [172063](#) (TPA-Capable  
Terminals Only)