

**NOTE:**

**ELECTRICAL:**

- 1. VOLTAGE RATING : 125V AC RMS
- 2. CURRENT RATING : 1.5A mp
- 3. CONTACT RESISTANCE : 100 MILLI OHMS MAX
- 4. INSULATION RESISTANCE : 1000M OHMS MIN @ 500V DC
- 5. DIELECTRIC STRENGTH : 750V AC RMS 60Hz, 1MIN
- CAT. 6A PERMANENT LINK : CONFORM TO ANSI/TIA-568-C.2 IEC 11801 PL2 CLASS Ea

**Accessory:**

- 1. Instruction Sheet 1pcs

RoHS2.0 AND REACH COMPLIANT

PACKING: 1PC/PE BAG+brown box+LABEL 1

Designable

Suitable for central plate of the Germany Company Busch Jaeger and Jung

**ENVIRONMENTAL:**

- 1. STORAGE :  $-40^{\circ}$  TO  $+85^{\circ}$
- 2. OPERATION :  $0^{\circ}$  TO  $+70^{\circ}$
- RJ45 JACK COMPLY TO REQUIREMENTS OF IEC-60603-7-5
- MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68


**MECHANICAL**

- 1. COVER&SHUTTER: FLAME RETARDANT ABS
- 2. JACK HOUSING : PBT+15%GF UL94V0
- 3. PCB : FR-4 THINKNESS:1.6MM
- 4. CONTACT MATERIAL: PHOSPHOR BRONZE T=0.35MM 8P8C 3u"Gold Plated
- 5. IDC CONTACT : PHOSPHOR BRONZE T=0.50MM WITH NICKEL PLATING
- 6. MOUNTING BRACKET: ZINC ALLOY#3
- 7. TOP COVER : ZINC ALLOY#3
- 8. RJ45 JACK LIFE: 750 TIMES MIN
- 9. IDN LIFE : 200 TIMES MIN
- 10. WIRE : AWG 22-24 Cable Conductor OD:0.65MM-0.5MM
- 11. IDC BODY :Krone Type Fireproof PC/ABS UL-94V0/  
With Colour Coded Printing T568A/B
- 12. RETENTIVENESS OF INSERTION STRUCTURE: 50N 60±5s


ITEM NO.	COLOUR
S216357	RAL9010

**SYNERGY 21**


UPDATE PACKING TYPE				2018-03-20	A2	CUSTOMER	ITEM NO.	S216357			
UPDATE				2014-06-11	A1	PRODUCT NAME	CAT.6A WALL OUTLET Horizontal cable entry	MANUFACTURE COUNTRY:	CHINA	UNIT	MM
NEW				2014-05-12	A	DRAWNBY	CHECKBY	APPOBY	DATE		
BY	CHK	REVISION RECORD MODIFICATIONS			DATE	REV.	SYNERGY 21	SYNERGY 21	SYNERGY 21	2018-03-20	




Face plate+pe bag





walloutlet+pe bag



1pcs/small box+user guide+label 1



Label 1





SHIPPING MARK

SIDE MARK



PO NO. :  
REACH and ROHS 2.0 Compliant  
MADE IN CHINA

PO NO. :  
Item no:  
Q' TY:  
N. W  
G. W  
Carton no.  
MEAS.



64PCS/ Carton bag+label 1

1. Packing: 1PCS/PE Bag+Inner Carton +instruction+ Label 1, 64PCS/ Carton bag+label 1

2. “工” type sealing

3. “井” type packaging

<b>SYNERGY 21</b>							
CUSTOMER				ITEM NO.	S216357		
PRODUCT NAME	PACKING	MANUFACTURE COUNTRY:		CHINA	UNIT	MM	
DRAWNBY		CHECKBY		APPOBY		DATE	
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.	SYNERGY 21	2018-03-20

UPDATE PACKING TYPE				2018-03-20	A2
NEW				2014-06-11	A
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.