

AP30 - Dermi Pro Glove

Collection: Aqua Gloves

Range: Gloves

Materials: Nylon, Nitrile, Nitrile Foam

Dipping: Nitrile
, Nitrile Foam

Inner Pack: 12

Outer Carton: 216

Product information

This fully dipped nitrile coated glove with foam nitrile coating in the palm area provides comfort and touch sensitivity. An elastic knit cuff holds it firmly on the arm for enhanced fit. The nitrile coating offers excellent liquid barrier while the superior foam dip ensures excellent grip even in oily environments.

Aqua Gloves

The ultimate barrier to water, liquids and non-aggressive substances. The Aqua range includes both highly water resistant and water proof gloves.

Gloves

A wide and increasing range of Hand Protection styles is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

AS/NZS 2161 .2

AS/NZS 2161 .3

ANSI/ISEA 105: 2016 CUT Level (A1)

EN 420 (Dexterity 5)

EN388:2016 +A1:2018 - (4.1.2.1.X)



Features

- CE certified
- Superb abrasion and tear resistance
- Fully coated for maximum liquid protection
- Nitrile foam coating for excellent grip in wet and dry conditions
- Ergonomic design to reduce hand fatigue
- 13 gauge liner for a perfect fit
- Retail tag which aids presentation for retail sales

	Range
	S/7 - XXL/11

PORTWEST®

PRODUCT SPECIFICATION & TECHNICAL DATA

AP30 - Dermi Pro Glove

Commodity Code: 6116108000

Test House

CTC (Notified Body No.: 0075)

4, rue Hermann Frenkel

Cedex 07, France

Cert No: 0075/2085/162/02/19/0562

CARTON DIMENSIONS/WEIGHT

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m ³)	EAN13	DUN14
AP30O8RS	Orange/Black	65.0	40.0	50.0	0.0690	0.1300	5036108277841	15036108767950
AP30O8RM	Orange/Black	65.0	40.0	50.0	0.0740	0.1300	5036108277834	15036108767943
AP30O8RL	Orange/Black	65.0	40.0	50.0	0.0830	0.1300	5036108277827	15036108767936
AP30O8RXL	Orange/Black	65.0	40.0	50.0	0.0860	0.1300	5036108277858	15036108767967
AP30O8RXXL	Orange/Black	65.0	40.0	50.0	0.0940	0.1300	5036108277865	15036108767974