

Hinged-door cabinet with doors with viewing window, width 1200 mm

With shelves

Application:

For secure and clearly-visible storage of tools, accessories, files or many other parts.

Execution:

- Stable welded steel sheet structure with base
- With doors with viewing window with shatter-proof acrylic glass
- zinc-plated shelves, height-adjustable in increments of 17 mm, load capacity per shelf 80 kg with evenly distributed weight
- Inset-type doors with internal pivot pins, doors internally reinforced by box profile, double-edged on all sides
- locks by means of a turning handle with integrated cylinder lock, includes 3 keys 2 keys

Delivery:

Shelves with load capacity of 100 kg with evenly distributed load, DOM locking system (fits HK tool cabinets, HK tool shelves, HK workbenches) and other colours available upon request.



Art. no.	50045 230
Brand	PAVOY
Manufacturer Part Number	3 1310-120-590-7357 16
Door design	Inspection glass
Width	1200 mm
Depth	500 mm
Height	1950 mm
Number of shelves	4 PCS
Load-carrying capacity per shelf	80 kg
Load-carrying capacity	400 kg
With partition wall	No
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Gross Weight	77.000 kg
Product Group	5CB