

## ABS-260-RC 40x5.0tmm 16OHM DYNAMIC SPEAKER

SPEAKERS

Specifications	ABS-260-RC
Rated impedance 2.0k Hz/1.0Vrms	16±15%Ω
Rated input power	0.5W
Max. input power	1.0W
Resonant frequency F <sub>0</sub>	510±20%Hz
Frequency range	F0Hz-6,000Hz
Sound pressure level at (AVG 0.8, 1.0,1.2, 1.5)KHz	84±3dB 1W/0.5m 94±3dB 0. 1W/0.1m
Magnet (NdFeB)	dia. 12.5mmx1.5mm
Cone material	Mylar
Housing material	Metal
Operating temperature	-20°C~+60°C
Storage temperature	-30°C~+60°C
Weight	9.2g

