


MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet **FirestoP®**

tasker® C224 – 1x0,08 (75Ω) +2x0,22 mm²
Special Video Cable



CATEGORY Special Video Cable 75Ω (See video Catalogue)

A: Black Soft **Flame Retardant PVC**. Outer Diam. Ø 4,80 (± 0,10) mm

75 Ω Video Coax:

B: Black Inner Sheath in **Flame Retardant PVC**. Diam. Ø 2,80 (± 0,10) mm.

C: Spiral Shielding in O.F.C. tinned Copper, covering 100%.

D: White Dielectric in **PEE**. Diam. Ø 1,50 (± 0,10) mm.

E: Stranded O.F.C. red copper formation 10x0,10 mm.
 Nom. Cross section 1x0,08 mm².

Insulated cores:

F: Inner Sheaths in **Flame Retardant PVC**. Colored one Red and one Black.
 Diam. Ø 1,20 (± 0,10) mm.

G: Stranded formations 7x0,20 mm in O.F.C. tinned copper.
 Nom. Cross section 2x0,22 mm².



MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

MARKING

tasker® C224 1x0,75 OHM+ 2x0,22 ²mm O.F.C. Special Video Cable FirestoP®
 CEI 20-22 II MADE IN ITALY

CUSTOM

This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

Coaxial Properties

Insulated Conductors Resistance	90 Ω/Km ± 5%
Coax Conductor Resistance	210 Ω/Km ± 5%
Coax Capacity Core/Shield	67 pF/mt
Coax Velocity of Propagation	66%
Coax Impedance	75 Ω ± 3%
Max Rated Voltage	49V
Operative Temperature	-20/+70°C

Attenuation dB/100 mt.

50 MHz	19,5
100 MHz	28,5
200 MHz	41,7
400 MHz	60,2
800 MHz	87,3
1000 MHz	103,0

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 27.06.2016
		Outdoor Direct Burial	Esterno Interrato			Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		