Product Specification PDF



Date	Correct as of 6th Aug 2019
Brand	C.K
Product	T3884
Description	Ecotronic ESD Reverse Angle Side Cutters (Micro)
Barcode	5013969938845
Commodity code	8203200000
Country of origin	TW



Features & Benefits

Lightweight, precision side cutters for fine cutting applications (e.g Microelectronics and fine mechanics) Suitable for cutting soft copper wires of up to $1.3 \text{mm} \varnothing / 16 \text{AWG}$ Special reverse action cutting blades \sim for accurate cutting of DIP pins on integrated circuits Micro, tapered head for greater access in confined spaces Sharp, precision ground cutting edges with a full flush cut Special tool steel blade, hardened for long-term cutting performance Elecro-static discharging handles \sim dissipative 10? Contoured, dual component handle design for comfortable working Black oxidised finish for corrosion resistance and reduced glare Smooth-action return spring for convenience during repetitive work Joint with durable stainlesss steel rivet Technical information: Total length: 132 mm Blade length: 8 mm Cutting angle: 48° Head Height (from joint to tip): 13 mm Head Width (Widest point): 9,5 mm Steel Thickness: 2 mm Cutting Capacity (Copper only): 1,3 mm / 16 AWG

Applicable Standards IEC 61340 5.1 & 5.2 Health & Safety None applicable

Warranty C.K products are guaranteed for 1 year against imperfect materials or workmanship. Damage caused through normal

wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures					
	Product only	Product & primary packaging	Secondary packaging	Transit packaging	
Item Quantity	1	1	6	120	
Width mm	132	220	21.6	300	
Depth mm	70	80	8.4	350	
Height mm	20	2.5	10.8	300	
Weight	64	79	543	11.5	
Packaging Information	Card use	0	Box	Case	
	Card gms	0	69	675	
	Plastic use	Blister	0	-	
	Plastic gms	15	0	0	
	Metal use	0	0	-	
	Metal gms	0	0	0	
	Timber use	0	0	-	
	Timber gms	0	0	0	