



SIMATIC ET 200SP, BASEUNIT BU20-P8+A4+0B, BU-TYPE F0, PUSH-IN KLEMMEN, WITH AUX-TERMINALS, BRIDGED TO LEFT BU WXH: 20MMX117MM

Product type designation	
Supply voltage	
Rated value (DC)	See manual
Rated value (AC)	See manual
Current carrying capacity	
up to 60 °C, max.	10 A
Galvanic isolation	
between backplane bus and supply voltage	Yes
Between process terminals and supply voltage	Yes
Between power bus and supply voltage	Yes
Isolation	
Isolation checked with	3250V DC 1min (type test), 2545V DC 2s (routine test)
Ambient conditions	
Ambient temperature in operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	0 °C
• vertical installation, max.	50 °C
Dimensions	
Width	20 mm
Height	117 mm
Weights	

Weight, approx.

48 g

last modified:

12.03.2015