

## Data sheet

### CM 201 (201-1AA00)

#### Technical data

<b>Order no.</b>	<b>201-1AA00</b>
------------------	------------------

Type	CM 201
------	--------

#### General information

Note	-
------	---

Features	Dual terminals 2x11 clamps, gray/gray Passive
----------	---

#### Clamp parameter

Terminal voltage max.	DC 60 V
-----------------------	---------

Terminal current max.	10 A
-----------------------	------

#### Isolated group

Number of clamps	11-11
------------------	-------

Color of clamps	grey-grey
-----------------	-----------

Binding of potential	unbound-unbound
----------------------	-----------------

Potential group current, max.	10 A-10 A
-------------------------------	-----------

#### Housing

Material	PPE / PA 6.6
----------	--------------

Mounting	Profile rail 35 mm
----------	--------------------

#### Mechanical data

Dimensions (WxHxD)	25.4 mm x 76 mm x 80 mm
--------------------	-------------------------

Weight	90 g
--------	------

#### Environmental conditions

Operating temperature	0 °C to 60 °C
-----------------------	---------------

Storage temperature	-25 °C to 70 °C
---------------------	-----------------

#### Certifications

UL508 certification	yes
---------------------	-----