

SA 1006	Mot	LIN-IC	Diode-Matrix-Encoder, 16 -4 Bit	16-DIP	-	-	-
SA 1008	Itt	PMOS-IC	TV, Progr.-Nr.(1...16)Einblendung/Channel No.	18-DIP	-	-	-
SA 1010 B	Itt	MOS-IC	US-FB Decoder, 15 Codes	16-DIP	-	-	-
SA 1020	Itt	CMOS-IC	US-FB Decoder, Speicher/Memory	16-DIP	-	-	-
SA 1021	Itt	MOS-IC	US-FB Empfängersteuerung/Receiver Control	24-DIP	-	-	SA 1121
SA 1022	Itt	MOS-IC	TV, Zeichenanzeige/Character Display	16-DIP	-	-	-
SA 1024	Itt	MOS-IC	US-FB Sender/Transmitter, 30 Codes	16-DIP	SA 1024*	16-DIP	M 1024, SA 1124
SA 1025	Itt	PMOS-IC	US-FB Empfänger/Receiver, 30 Codes	16-DIP	SA 1025	16-DIP	M 1025
SA 1027 N	Phi	LIN-IC	Schrittmotor-/Stepper Motor Controller	16-DIP	-	-	-
SA 1029(N6)	Phi	LIN-IC	Logic- & Interface-Steuerung/Control	16-DIP	-	-	D 410D
SA 1042	Mot	LIN-IC	Schritt-/Stepper Motor Drv, 6 & 12V	12-DIP+8	-	-	-
SA 1042 A	Mot	LIN-IC	=SA 1042: f. 24V-Motor	12-DIP+8	-	-	-
SA 1043	Phi	CMOS-IC	VC, Sync. Signal, PAL/SECAM/NTSC	28-DIP	-	-	-
SA 1043 T	Phi	CMOS-IC	=SA 1043: SMD	28-MDIP	-	-	-
SA 1044	Phi	CMOS-IC	Color Processor, PAL/SECAM/NTSC	16-DIP	-	-	-
SA 1044 T	Phi	CMOS-IC	=SA 1044: SMD	16-MDIP	-	-	-
SA 1045(P)	Phi	CMOS-IC	Leitungstreiber & Empf./Line Driver & Receiver	8-DIP	-	-	(SA 1235)
SA 1045 T	Phi	CMOS-IC	=SA 1045: SMD	8-MDIP	-	-	-
SA 1050	Itt	CMOS-IC	IR-FB Sender/Transmitter, 64 Codes	24-DIP	SA 1250	24-DIP	SA 1250
SA 1051	Itt	PMOS-IC	IR-FB Empfänger/Receiver, 64 Codes	24-DIP	SA 1251	24-DIP	SA 1251
SA 1056 P	Phi	CMOS-IC	AM/FM Frequ.-Synthesizer	16-DIP	-	-	U 810D
SA 1057	Phi	LIN-IC	AM/FM PLL Frequ.-Synthesizer	18-DIP	-	-	-
SA 1058	Phi	LIN-IC	=SA 1059	-	-	-	SA 1059
SA 1059	Phi	LIN-IC	Frequ.-Teiler/Divider, 1:32/33	16-DIP	-	-	-
SA 1060	Phi	LIN-IC	LED Display Interface, 32 Segments, Duplex	24-DIP	-	-	-
SA 1061	Phi	NMOS-IC	LED Display Interface, 16 Segments	24-DIP	SA 1061*	24-DIP	-
SA 1062(A)	Phi	LIN-IC	LCD Display Drv, Interface	28-DIP	-	-	-
SA 1062(AT)	Phi	LIN-IC	=SA 1062(A): SMD	28-MDIP	-	-	-
SA 1063	Phi	LIN-IC	FLT Display Interface	24-DIP	-	-	-
SA 1064(P)	Phi	LIN-IC	LED Drv, 4 Digits, I ² C-Bus	24-DIP	-	-	-
SA 1064 T	Phi	LIN-IC	=SA 1064: SMD	24-MDIP	-	-	-
SA 1070	Phi	LIN-IC	Frequ.-Zähler/Counter, Display Interface	28-DIP	-	-	-
SA 1071	Itt	PMOS-IC	IR-FB Adapter f. SA 1051	-	-	-	-
SA 1072	Itt	LIN-IC	TV, UHF Verstärker f. Digital Tuning	14-DIP	-	-	-
SA 1073	Itt	LIN-IC	TV, UHF Teiler/Divider f. Digital Tuning	14-DIP	-	-	-
SA 1074	Itt	PMOS-IC	TV, Digital Tuning Controller	24-DIP	SA 1274	24-DIP	SA 1274
SA 1075	Itt	PMOS-IC	TV, Digital Tuning (Speicher/Memory)	18-DIP	SA 1075	18-DIP	-
SA 1076	Itt	PMOS-IC	TV, Digital Tuning (Anzeige/Display)	18-DIP	-	-	SA 1276
SA 1080	Itt	NMOS-IC	CTV, Spieleadapter/Games Adaptor	18-DIP	-	-	-
SA 1082 P	Phi	IC	US-FB Sender/Transmitter	28-DIP	-	-	-
SA 1094(-2)	Itt	CMOS-IC	Telefon-Tonruf/Telephone Sound Alarm	14-DIP	-	-	-
SA 1099	Phi	LIN-IC	Music Synthesizer, stereo	18-DIP	-	-	-
SA 1101(P)	Phi	MOS-IC	Universal Sync. Generator	28-DIP	-	-	-
SA 1101 T	Phi	MOS-IC	=SA 1101(P): SMD	28-MDIP	-	-	-
SA 1121	Itt	PMOS-IC	US-FB Empfängersteuerung/Receiver Control	24-DIP	-	-	-
SA 1124	Itt	CMOS-IC	US-FB Sender/Transmitter, 30 Codes	16-DIP	SA 1124	16-DIP	M 1124
SA 1130	Itt	PMOS-IC	US-FB Empfänger/Receiver, 30 Codes	18-DIP	SA 1130*	18-DIP	M 1130
SA 1131 P	Phi	LIN-IC	PCM Audio Error Corrector 1 (ECO-1)	40-DIP	-	-	-
SA 1131 T	Phi	LIN-IC	=SA 1131P: SMD	40-MDIP	-	-	-
SA 1132 P	Phi	LIN-IC	PCM Audio Error Corrector 2 (ECO-2)	20-DIP	-	-	-
SA 1132 T	Phi	LIN-IC	=SA 1132P: SMD	20-MDIP	-	-	-
SA 1133 P	Phi	LIN-IC	PCM Audio A/D Interface (ADI)	24-DIP	-	-	-
SA 1133 T	Phi	LIN-IC	=SA 1133P: SMD	24-MDIP	-	-	-
SA 1136 P	Phi	LIN-IC	PCM Audio Ident-Word Interface (IDI)	20-DIP	-	-	-
SA 1136 T	Phi	LIN-IC	=SA 1136P: SMD	20-MDIP	-	-	-
SA 1174	Itt	PMOS-IC	=SA 1274: England Version	24-DIP	-	-	-
SA 1176	Itt	MOS-IC	TV, Digital Tuning (Anzeige/Display)	18-DIP	-	-	SA 1276
SA 1220	Itt	PMOS-IC	TV, Speicher/Memory	18-DIP	-	-	-
SA 1224	Itt	CMOS-IC	US-FB Sender/Transmitter, 30 Codes	16-DIP	-	-	-
SA 1230	Itt	PMOS-IC	US-FB Empfänger/Receiver, 30 Codes	18-DIP	-	-	-
SA 1235	Phi	CMOS-IC	Leitungstreiber & Empf./Line Driver & Receiver	8-DIP	-	-	(SA 1045)
SA 1250	Itt	CMOS-IC	IR-FB Sender/Transmitter, 64 Codes	24-DIP	SA 1250	24-DIP	-
SA 1251	Itt	PMOS-IC	IR-FB Empfänger/Receiver, 64 Codes	24-DIP	SA 1251	24-DIP	-
SA 1271	Itt	PMOS-IC	IR-FB Adapter f. SA 1251	18-DIP	-	-	-
SA 1272	Itt	NMOS-IC	IR-FB Adapter f. SA 1251	18-DIP	-	-	-
SA 1274	Itt	PMOS-IC	TV, Digital Tuning Controller	24-DIP	SA 1274*	24-DIP	-
SA 1276	Itt	PMOS-IC	TV, Digital Tuning (Anzeige/Display)	18-DIP	SA 1276*	18-DIP	-
SA 1280	Itt	NMOS-IC	TV, Tuning, Bedienung/Control	40-DIP	-	-	-
SA 1281		MOS-IC	FB Controller	40-DIP	-	-	-
SA 1282		MOS-IC	FB Controller	40-DIP	-	-	-
SA 1283		MOS-IC	FB Controller	40-DIP	-	-	-
SA 1288 A		MOS-IC	FB	40-DIP	-	-	-
SA 1289 B		MOS-IC	FB	40-DIP	-	-	-
SA 1290	Itt	NMOS-IC	TV, Tuning, FB Empfänger/Receiver	40-DIP	-	-	-
SA 1291		IC		-	-	-	-
SA 1292		IC		-	-	-	-
SA 1293	Itt	NMOS-µC-IC	TV-FB Empfänger/Receiver	40-DIP	-	-	-
SA 1293-2,-02	Itt	NMOS-µC-IC	=SA 1293: kundenspezifisch/customized	40-DIP	-	-	-
SA 1293-3,-03	Itt	NMOS-µC-IC	=SA 1293: kundenspezifisch/customized	40-DIP	SA 1293-3	40-DIP	-
SA 1293 A(-3,-03)	Itt	NMOS-µC-IC	=SA 1293	40-DIP	SA 1293 A-03	40-DIP	-
SA 1294		IC		-	-	-	-
SA 1296		MOS-IC	FB	40-DIP	-	-	-
SA 1300	Phi	LIN-IC	Tuner Switch, 5x Drv, 5x 100mA, I ² C-Bus	9-SIL	-	-	-
SA 1310	Phi	LIN-IC	VC(VHS), Control Interface	18-DIP	-	-	-
SA 1310 T	Phi	LIN-IC	=SA 1310: SMD	20-MDIP	-	-	-
SA 1350	Itt	CMOS-IC	IR-FB Sender/Transmitter, 64 Codes	18-DIP	SA 1350*	18-DIP	-
SA 1351	Itt	NMOS-IC	IR-FB Empfänger/Receiver, 64 Codes	24-DIP	-	-	-
SA 1500	Phi	MOS-IC	Accu Ladungsanzeige/Remaining Energy Indicator	20-MDIP	-	-	-
SA 1760	Phi	MOS-IC	D2MAC Video Decompression, Descramble, I ² C	68-PLCC	-	-	-
SA 1770	Phi	MOS-IC	D2MAC Digital MAC Packet, I ² C-Bus	68-PLCC	-	-	-
SA 1900	Itt	PMOS-IC	Spielzeugorgel/Toy Organ	24-DIP	-	-	-
SA 2008	Itt	PMOS-IC	TV, Progr.-Nr.(1...16) Einblendung/Channel No.	18-DIP	-	-	-
SA 2520 GP	Phi	MOS-IC	MPEG Audio Compression Stereo Filter/CODEC	44-MP	-	-	-