

## Product information

# 78 81 125

## Electronic Super Knips®

DIN ISO 9654



- Precision-ground cutting edges with very small bevel suitable also for hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Special tool steel, burnished
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Precisely shaped tips cut wires close to a surface from  $\varnothing 0.2$  mm
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter




### General

Article No.	78 81 125
EAN	4003773065074
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	57 g
Dimensions	125 x 50 x 16 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	$\varnothing 1.2$ mm
Cutting capacities hard wire (diameter)	$\varnothing 0.6$ mm
Cutting capacities soft wire (diameter)	$\varnothing 0.2 - 1.6$ mm
Jaw length (B)	9 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	13.5 mm



technical change and errors excepted