

Solid carbide end mill

4 cutting edges, TiAlN-coated


ORION[®]

Application:

End mill for universal machining of non-ferrous metals.

Execution:

- solid carbide ultra-fine grain
- straight shank in accordance with DIN 6535 HB
- TiAlN-coated
- centre cutting
- with edge protection chamfer



Art. no.	16828 020
Brand	ORION
Manufacturer Part Number	16828020
Cutting material	SC
Surface	TiAlN
Type	W
Number of cutting edges	4 PCS
Twist angle	45°
Tool holding device	HB parallel shank
Construction length	Normal
Cutting edge diameter	2 mm
Cutting edge length	8 mm
Length	57 mm
Edge protection chamfer length	0.05 mm
Shank diameter	6 mm
fz aluminium	0.01 mm
Gross Weight	0.020 kg
Overall stainless steel suitability	2
fitness not iron total	1
fitness Titan/Nickel/Super total	2
Product Group	154

EAN

4039247455515