

## Clamping tool assortment in box



### Application:

This assortment contains all of the requisite elements for quick clamping of workpieces or equipment on T-groove tables.

### Execution:

- All parts made of heat-treated steel

### Delivery:

Assortment in wooden case



<b>Art. no.</b>	<b>26153 012</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	83592
<b>Suitable for groove width</b>	12
<b>Min. clamping height with 2 clamping points</b>	2 mm
<b>Thread dimension</b>	M12
<b>Max. clamping height with 2 clamping points</b>	270 mm
<b>Min. clamping height with 4 clamping points</b>	2 mm
<b>Max. clamping height with 4 clamping points</b>	160 mm
<b>Wooden box length</b>	460 mm
<b>Wooden box width</b>	330 mm
<b>Wooden box height</b>	50 mm
<b>Number of DIN 787 T-slot screws</b>	2 x 50 mm, 4 x 80 mm, 4 x 125 mm
<b>Weight</b>	14.3 kg
<b>Number of DIN 6379 stud bolts (extension pin)</b>	4 x 100 mm
<b>Number of DIN 6330 B high nuts</b>	6 PCS
<b>Number of rounded washers and ball sockets DIN 6319 G</b>	6 PCS
<b>Number of extension nuts</b>	4 PCS
<b>Gross Weight</b>	14.400 kg
<b>Product Group</b>	260

### EAN

4020772083595