

Clamping tool assortment in box



Application:

This assortment contains all of the requisite elements for quick clamping of workpieces or equipment on T-groove tables.

Version:

- All parts made of heat-treated steel

Delivery:

Assortment in wooden case



Art. no.	26153 012
Suitable for groove width	12
Min. clamping height with 2 clamping points	2 mm
Thread dimension	M12
Max. clamping height with 2 clamping points	270 mm
Min. clamping height with 4 clamping points	2 mm
Max. clamping height with 4 clamping points	160 mm
Wooden box length	460 mm
Wooden box width	330 mm
Wooden box height	50 mm
Number of DIN 787 T-slot screws	2 x 50 mm, 4 x 80 mm, 4 x 125 mm
Weight	14.3 kg
Number of DIN 6379 stud bolts (extension pin)	4 x 100 mm
Number of DIN 6330 B high nuts	6 PCS
Number of rounded washers and ball sockets DIN 6319 G	6 PCS
Number of extension nuts	4 PCS

EAN-Code

4020772083595