

## Electronic micrometer

Micromar 40 EWRI IP65



### Application:

for measuring e.g. shaft diameters, external dimensions of workpieces etc.

### Execution:

- carbide-tipped measuring faces
- RESET (resetting the display)
- ABS (display can be set to zero without losing the reference to the ORIGIN)
- mm/inch
- ORIGIN (measurement pre-setting)
- LOCK function (keypad lock)
- TOL (input of tolerances and warning limits)
- DATA (in connection with data connection cable)
- HOLD (measured value storage)

### Delivery:

operating instructions, battery, setting gauge (from a measuring range of 25–50 mm), travel case



<b>Art. no.</b>	<b>31403 325</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4157101
<b>Display</b>	Digital
<b>Min./max. length measuring range</b>	25-50 mm
<b>Digit increment</b>	0.001 mm
<b>Measuring surface diameter</b>	6.5 mm
<b>IP protection class</b>	IP 65
<b>Data transmission type</b>	MarConnect
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>Measuring spindle increments</b>	0.5 mm
<b>Calibration Group</b>	D, E
<b>Gross Weight</b>	0.800 kg
<b>Product Group</b>	305

### EAN

4059192058760