

Electronic micrometer head

0–25 mm, Digimatic, 12/18 mm stem, IP65

Mitutoyo

Application:

For integration in measuring and pre-adjustment devices and for use as setting and control elements in machine tools

Execution:

- Plain drive arbour
- With locking mechanism
- LCD, digit size 7.5 mm

Advantage:

- Water-resistant and dustproof (IP65 degree of protection)



Art. no.	32017 634
Brand	MITUTOYO
Manufacturer Part Number	350-27 1-30
Display	Digital
Min./max. length measuring range	0-25 mm
Digit increment	0.001 mm
Measuring surface diameter	6.35 mm
Measuring arrangement	Flat
Clamp in shank diameter	12 mm
Clamping shank length	16 mm
Coupling design	Slide coupling
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Functions	ABS function, Automatic switch-off, Preset function, Hold-function (AE lock)
IP protection class	IP 65
Design	Metric
Digit height	7.5 mm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	SR44
Data transmission type	DIGIMATIC
Calibration Group	DE
Gross Weight	0.300 kg
Product Group	3MA

EAN

4946368695976