

Workbench with manual height adjustment

Multiplex beechwood 1500 mm, height-adjustable via notches in the base

Execution:

- Base made of sturdy U-profile steel 80 x 50 x 2 mm, height x depth 800 x 630 mm, incl. cross strut between bases
- Working height adjustable via notches in the base in increments of 25 mm, from approx. 640-990 mm
- Delivered as individual parts, unassembled

Advantage:

- The workbench can be adjusted to the desired working height
- For perfect ergonomics in the workplace
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50185 051
Worktop width	1500 mm
Levelling	No
Worktop height	40 mm
Adjustable in height	Yes
Material of frame	Steel plate
Worktop depth	750 mm
Max. height adjustment	990 mm
Min. height adjustment	640 mm
Surface	Powder-coated
Load-carrying capacity	800 kg
Type	Height adjustable via hand crank
Material of worktop	Multiplex beech
Product Group	586

EAN

4053625138890