

Hinged-door cabinet with shelf and drawers

Doors with perforated panels

[®]RasterPlan

Application:

For clearly-arranged and space-saving storage of tools.

Execution:

- Welded sheet steel structure with rear wall, ¼ slotted/¼ perforated panel for attaching support elements
- Overlay, double-walled, twist-resistant hinged doors, opening angle over 200°
- Three-point security cylinder lock with recessed turning handle



| | |
|--|--|
| Art. no. | 50639 264 |
| Brand | RASTERPLAN |
| Manufacturer Part Number | 1460.04.3024 |
| Door design | Perforated boards |
| Width | 1000 mm |
| Depth | 600 mm |
| Height | 1950 mm |
| Number of shelves | 2 PCS |
| Shelf width | 1000 mm |
| Shelf depth | 600 mm |
| Load-carrying capacity per shelf | 80 kg |
| Number of drawers | 2 PCS |
| Drawer front height | 2 x 100 mm |
| With worktop | Yes |
| Load-carrying capacity per drawer | 110 kg |
| Pullout type | Full extension |
| With partition wall | No |
| Central locking | Yes |
| Lock type | Twist-grip lock with three-point fastening |
| Material | Sheet steel |
| Colour of front | Anthracite grey RAL 7016 |
| Surface | Lacquered |
| Cabinet colour | Light grey RAL 7035 |
| Gross Weight | 141.220 kg |
| Product Group | 5AC |

EAN

4251142237960