

Socket wrench set, 63 pieces

1/4" and 1/2" square drive DIN 3120



Execution:

- HPQ steel, die-forged
- chrome-plated, polished
- hex and TX inserts
- 52 socket wrench inserts, 11 operating tools

Advantage:

- Excellent load capacity thanks to tough, hard HPQ steel alloy
- Cadmium-free, therefore also suitable for working on titanium-alloy parts and titanium connecting elements
- High force transmission to the edges of the bolts and nuts for optimum load distribution
- Longer bolt and nut service lives

Delivery:

in robust, stackable ABS plastic storage box



Art. no.	58024 421
Brand	STAHLWILLE
Manufacturer Part Number	96013702
Tip type	Hexagon, Outer hexagon
Drive	1/4 inch, 1/2 inch
Sockets with hexagon-head tip provided	4 mm, 4.5 mm, 5 mm, 5.5 mm, 6 mm, 7 mm, 8 mm, 9 mm, 10 mm, 11 mm, 13 mm, 16 mm, 17 mm, 18 mm, 19 mm, 21 mm, 22 mm, 24 mm, 27 mm, 30 mm
Sockets with socket hexagon-head tip provided	3 mm, 4 mm, 5 mm, 6 mm, 8 mm, 10 mm, 12 mm, 14 mm
Sockets with socket hexagon head or external TX tip provided	E4, E5, E6, E7, E8, E10, E11, E12, E14, E16, E18, E20, E22, E24, TX8, TX9, TX10, TX15, TX20, TX25, TX27, TX30, TX40, TX45, TX50, TX55, TX60
Ratchets provided	1/4-inch square, 1/2-inch square
Extensions provided	54 mm, 130 mm, 150 mm, 255 mm
Cross handles provided	115 mm, 300 mm
Cardan joints provided	38 mm, 70 mm
Gross Weight	6.734 kg
Product Group	531

EAN

4018754261130