

Pneumatic drill machine D 13-900 P

MANNESMANN
DEMAG

Execution:

- Exhaust air noise damper lowered into pistol handle
- Ergonomic aluminium handle
- Compact construction

Advantage:

- Air feed through handle

Delivery:

Drill chuck key



Art. no.	75061 440
Brand	MANNESMANN DEMAG
Manufacturer Part Number	46920375
Model	D 13-900 P
Max. drilling diameter in steel	8 mm
Max. idle speed	900 rpm
Power rating	320 W
Air consumption	7 l/s
Connection thread	IT 1/4 inch
Min./max. drill chuck span width	1-13 mm
Inner hose diameter	8 mm
Weight	1.25 kg
With right/left-hand rotation	Yes
Length	234 mm
Sound-pressure level	75 dB
Gross Weight	1.250 kg
Product Group	7AA

EAN

4251757300646

