

## Pneumatic drill machine D 13-900 P

**MANNESMANN  
DEMAG**

### Version:

- Exhaust air noise damper lowered into pistol handle
- Ergonomic aluminium handle
- Compact construction

### Advantage:

- Air feed through handle

### Delivery:

Drill chuck key



<b>Art. no.</b>	<b>75061 440</b>
<b>Model</b>	D 13-900 P
<b>Max. drilling diameter in steel</b>	8 mm
<b>Max. idle speed</b>	900 rpm
<b>Power rating</b>	320 W
<b>Air consumption</b>	7 l/s
<b>Connection thread</b>	IT 1/4 inch
<b>Min./max. drill chuck span width</b>	1-13 mm
<b>Inner hose diameter</b>	8 mm
<b>Weight</b>	1.25 kg
<b>With right/left-hand rotation</b>	Yes
<b>Length</b>	234 mm
<b>Sound-pressure level</b>	75 dB

### EAN-Code

4251757300646