



Image for reference only

Product Number: 54648

Order Abbreviation: EGE

General Description: 500 watt, tungsten halogen, medium to high voltage, single-ended

Product Information

Abbrev. With Packaging Info.	EGE 120V 12/CS 1/SKU
ANSI Code	EGE
Application	STAGE & STUDIO
Average Rated Life (hr)	2000
Base	P28s Medium Prefocus
Bulb	T5
Class	C (GAS)
Color Rendering Index (CRI)	100
Color Temperature (K)	3000
Diameter d (in)	0.709
Diameter d (mm)	18.00
Distance a (in)	3.467
Distance a (mm)	88.9
Filament	CC-8
Lamp Finish	Clear
Length l (in)	5.698
Length l (mm)	146.1
Length l max. (in)	5.698
Length l max. (mm)	146.1
Light Center Length - LCL (in)	3.467
Light Center Length - LCL (mm)	88.9
Luminous Flux (lm)	10000
Maximum Overall Length - MOL (in)	5.698
Maximum Overall Length - MOL (mm)	146.1
Nominal Voltage (V)	120.00
Nominal Wattage (W)	500.00
Operating Position	ANY
Type of Current	AC