



PRODUKTINFORMATION

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

ELFA artikelnr

54-126-06 Fläkt 60x60mm 12VDC JF0615B1L

54-126-14 Fläkt 60x60mm 12VDC JF0615B1H

DC FAN

JAMICON®

60X60X15 mm



SPECIFICATIONS

Model	Bearing	Rated Voltage (V)	Operating (V)	Air Flow (CFM)	Static Pressure (mmH ₂ O)	Speed (R.P.M)	Rated Current (Amp)	Input Power (Watt)	Noise (dBA)	Life Expectancy (Hour)	Weight (g)
JF0615B1L	B	12	10.2~13.8	11.63	3.26	3500	0.12	1.44	25.1	64000	45
JF0615S1L	S			11.63	3.26	3500	0.12	1.44	25.1	38000	
JF0615B1M	B			13.28	4.12	4000	0.15	1.80	30.1	56000	
JF0615S1M	S			13.28	4.12	4000	0.15	1.80	30.1	33000	
JF0615B1H	B			15.74	5.41	4500	0.17	2.04	34.0	50000	
JF0615S1H	S			15.74	5.41	4500	0.17	2.04	34.0	30000	
JF0615B2L	B	24	20.4~27.6	11.63	3.26	3500	0.09	2.16	25.1	64000	
JF0615S2L	S			11.63	3.26	3500	0.09	2.16	25.1	38000	
JF0615B2M	B			13.28	4.12	4000	0.11	2.64	30.1	56000	
JF0615S2M	S			13.28	4.12	4000	0.11	2.64	30.1	33000	
JF0615B2H	B			15.74	5.41	4500	0.13	3.12	34.0	50000	
JF0615S2H	S			15.74	5.41	4500	0.13	3.12	34.0	30000	

Specifications Subject to change without notice

- Frame: Plastic Material UL 94V-0
- Blade: Plastic Material UL 94V-0
- Insulation Resistance: 50M ohm min. at 500 VDC (between frame and terminal)

- Dielectric Strength: 5mA max. at 500 VAC 60 Hz one minute (between frame and terminal)
- Operating Temperature: -10°C to +70°C
Option: -20°C to +80°C

