

SENCITY® SPOT-L WiFi Antenna 1354.17.0001

Description

Linear vertical or horizontal polarized WiFi antenna
 Frequency band 4.9 - 5.875 GHz, 23 dBi, WLAN
 WiFi IEEE 802.11a/h/p standard
 High gain directional antenna
 For outdoor applications
 Ingress protection IP67 (IEC 60529)



Product Configuration

Technical Data

Electrical Data

	Band 1	Band 2
Frequency (MHz)	4900 - 5150	5150 - 5875
VSWR	1.9	1.7
Impedance (Ohm)	50	50
Gain (dBi)	22	23
3dB beamwidth (h) (°)	9	9
3dB beamwidth (v) (°)	9	9
Composite power max (W)	6	
Ambient temperature (°C)	25	
Front to back ratio (dB)	35	35

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes

Connections

	Band 1	Band 2
Port 1	X	X

General Data

Mechanical Data

Dimensions (mm) 305 x 305 x 15 (Height x Width x Depth)
 Weight (kg) 1.2
 Windload frontal: 263 N at 160 km/h, lateral: 13 N at 160 km/h, Wind speed survival: 220 km/h

Environmental Data

Environmental conditions indoor/outdoor
 Operation temperature (°C) -45 to 70
 Storage temperature (°C) -45 to 70
 IP rating IP67
 Flammability rating UL 94-HB
 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant
 Lead-free soldered yes
 WEEE 2012/19/EU special marking needed
 REACH 1907/2006/EC compliant

SENCITY® SPOT-L WiFi Antenna 1354.17.0001

Temperature condition low -55°, IEC 60068-2-1
Temperature condition hig +71°, IEC 60068-2-2
Temperature cycling IEC 60068-2-14 1h -45°C to +70°C 3 cycles
Salt spray IEC 60068-2-11 Ka / 500 h
Humidity ETSI EN300-2-4 T4.1E / 144h / 95%
Solar radiation ASTM G53 / 1000 h
Mechanical shock EC 60721-3-4, 4M3
Vibration IEC 60721-3-4 30 min/axis random 4M3

Material Data

Radome colour	RAL 9002 (grey-white)
Radome material	Plastic
Back plate/base plate material	Aluminium

Related Products

9091.99.0183 Planar Antenna Downtilt Bracket

Related Documents

Mounting instruction	DOC-0000225623
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing	DPR-00265928
3D-model	DOC-0000459244