

FEATURES

- High quality nylon tyre
- Swivel castors
- Non-slip rubber feet
- Vibration damping rubber feet

RS PRO Swivel Swivel Castor, 250kg Load Capacity, 50mm Wheel Diameter

RS Stock No.: 611-4420



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO castors are a range of multifunction levelling castors. These wheels are versatile and are an ideal choice for equipment that needs to be mobile, but when in place is completely firm and stationary. They can be used in numerous applications such as Vending machines, Medical appliances and Workstations. The plate is steel with a khaki powder coating whilst the bracket is aluminium die-casting, also featuring bi-level balls upon balls for full swivel.

General Specifications

Rotation	Swivel
Weight Class	Heavy Duty
Load Capacity	250kg /1pcs
Load Capacity / 4pcs	500kg
Tyre Material	Nylon
Hub Material	Nylon
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Vending machines, Medical appliances, Workstations, Measuring Instruments

Mechanical Specifications

Mounting Type	Plate
Wheel Diameter	50mm
Wheel / Tread Width	25mm
Overall Height	82mm
Number of Fixing Holes	4
Fixing Hole Size	7mm
Hub Bearing Type	Ball Bearing
Levelling Extent	10mm
Offset	36mm

Fixing Centres Specifications	
Fixing Centres	73mm x 73mm
Fixing Centres (Length)	73mm
Fixing Centres (Width)	73mm

Fixing Plate Specifications	
Fixing Plate Dimensions	58mm x 58mm
Fixing Plate Length	58mm
Fixing Plate Width	58mm

Operation Environment Specifications

Operating Temperature	-10°C to 90°C
-----------------------	---------------





