


SCHRAUBEN UND MUTTERN AUS NYLON

Sechskantmuttern

SR 1954

Nylon 6.6, natur

- Maßtoleranzen ähnlich NF E 2403, ISO 4032, DIN 555, DIN 934




Artikelnummer	Maße (mm)			Stück/VPE
	d	H	S	
0030140000VR	M2 x 0.4	1.6	4.0	1000
468786	M2.5 x 0.45	2.0	5.0	1000
496239	M3 x 0.5	2.4	5.5	1000
496240	M4 x 0.7	3.2	7.0	1000
0030030000VR	M5 x 0.8	4.2	8.0	1000
0030040000VR	M6 x 1.0	5.0	10.0	1000
0030050000VR	M8 x 1.25	6.5	13.0	1000
0030060000VR	M10 x 1.5	8.0	17.0	1000
0030070000VR	M12 x 1.75	10.8	18.0	500
0030080000VR	M14 x 2.0	12.8	21.0	500
0030090000VR	M16 x 2.0	14.8	24.0	250
0030110000VR	M20 x 2.5	18.0	30.0	250
0030120000VR	M24 x 3.0	21.5	36.0	250

Selbstkantmuttern mit Flansch

SR 1966

Nylon 6.6, natur




Artikelnummer	Maße (mm)				Stück/VPE
	d	D	H	s	
43534	M3 x 0.5	7.0	3.2	5.5	1000
43535	M4 x 0.7	9.4	4.1	7.0	1000
43536	M5 x 0.8	11.0	5.1	8.0	1000
43537	M6 x 1.0	13.0	6.0	10.0	1000
43538	M8 x 1.25	17.0	8.0	13.0	1000
43539	M10 x 1.5	22.0	9.5	16.0	1000
0590070000VR	M12 x 1.75	28.0	14.4	18.7	500
0590090000VR	M16 x 2.0	36.0	15.8	23.7	100

Sechskantmuttern - schwarz

SR 1954

Nylon 6.6, schwarz

- Maßtoleranzen ähnlich NF E 2403, ISO 4032, DIN 555, DIN 934




Artikelnummer	Maße (mm)			Stück/VPE
	d	H	S	
496241	M3 x 0.5	2.4	5.5	100
496242	M4 x 0.7	3.2	7.0	100
0030030001VR	M5 x 0.8	4.2	8.0	100
0030040001VR	M6 x 1.0	5.0	10.0	100
0030050001VR	M8 x 1.25	6.5	13.0	100
0030060001VR	M10 x 1.5	8.0	17.0	100
0030070001VR	M12 x 1.75	10.8	18.0	100

Selbstsichernde Sechskantmuttern

SR 1987

Nylon 6.6, natur



Artikelnummer	Maße (mm)				Stück/VPE
	d	D	H	s	
0600020000VR	M4 x 0.7	8.3	5.5	7.0	1000
0600030000VR	M5 x 0.8	9.5	6.5	8.0	1000
0600040000VR	M6 x 1.0	11.4	7.3	10.0	1000
0600050000VR	M8 x 1.25	16.2	9.0	14.0	1000