## 75W ENCLOSED POWER SUPPLY RANGE



STONTRONICS: SRS-75-12, SRS-75-24, SRS-75-36, SRS-75-48

#### **Features:**

- Universal / Full range AC input
- Built in active PFC
- Highly reliable design
- Built in remote sense function
- 3 years warranty



### **Description:**

The 75W enclosed power supply range has been specially designed to offer high efficiency, long life and high reliability for use in a variety of applications. This range comprises of 4 models with outputs of either 12v,24v,36v or 48v. Each model is RoHS, CE, UL approved and come with a three year warranty.

		SPECIFICATION			
PART NUMBER	SRS-75-12	SRS-75-24	SRS-75-36	SRS-75-48	
DC VOLTAGE	12V	24V	36V	48V	
RATED CURRENT	6A	3.2A	2.1A	1.6A	
CURRENT RANGE	0~6A	0~3.2A	0~2.1A	0~1.6A	
RATED POWER	72W	76.8W	75.6W	76.8W	
RIPPLE & NOISE	120mVp-p	150mVp-p	200mVp-p	200mVp-p	
VOLTAGE REGULATION RANGE	±10.0%				
VOLTAGE ACCURACY	±1.0%				
LINE ADJUSTMENT	±0.5%				
LOAD ADJUSTMENT RATE	±0.5%				
RISE	500ms, 30ms/230VAC 100% Load				
HOLD UP TIME	60ms/ 230VAC 12ms/115VAC Full Load				
VOLTAGE RANGE	100~240VAC				
FREQUENCY	47~63Hz				
EFFICIENCY	88%	90%	92%	92%	
ALTERNATING CURRENT	1.4A/115VAC, 0.85A/230V				
INRUSH CURRENT	50A/230VAC				
LEAKAGE CURRENT	<3.5mA/240VAC				
OVRLOAD	100 ~ 150% of rated output				
SHORT CIRCUIT	Hiccup Mode, auto-recovery				
OVER VOLTAGE	115%-135% rated output voltage, constant voltage limited				
WORKING TEMP	-30°C ~ +50°C (See derating curve)				
WORKING HUMIDITY	10 ~ 95% RH (Non condensing)				
STORAGE TEMP	-40°C ~+85°C				
STORAGE HUMIDITY	10 ~ 95% RH (Non condensing)				
TEMP COEFFICIENT	±0.03%/°C(0~50°C)				
VIBRATION RESISTANCE	10~500Hz, 2G, 10min/cycle, X, Y, Z 60min in each direction				
SAFETY STANDARD	Design according to GB4943-2001, UL1012				
WITHSTAND VOLTAGE	I/P-O/P:3.0KV AC,	I/P-O/P:3.0KV AC, I/P-FG:2.0KV AC,O/P-FG:0.5KVAC			
ISOLATION RESISTANCE	I/P-O/P,I/P-FG,O/F	I/P-O/P,I/P-FG,O/P-FG:100MΩ/500VDC			
EMC	EN55022 CLASSB				
LIFETIME	100,000hours(25°0	100,000hours(25°C)			
SIZE	99×97×30(L*W*H)				
WEIGHT	0.3Kg/pc66pcs/carton				

# 75W ENCLOSED POWER SUPPLY RANGE



STONTRONICS: SRS-75-12, SRS-75-24, SRS-75-36, SRS-75-48

### **Diagrams**







