


Parts Information: **Transmission Jack Itonne Vertical Quick** Lift

Model No: 1000TRQ.V2



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information. IMPORTANT: No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR I: 01284 757500 01284 703534 sales@sealey.co.uk

💮 www.sealey.co.uk



Parts Information: **Transmission Jack Itonne Vertical Quick** Lift Model No: 1000TRQ.V2

Item	Part No.	Description	Item	Part No.	Description
I	1000TRQ.V2-01	Fork	29	300TRQ.V2-29	Inner pump piston
2	1000TRQ.V2-02	Oil Wiper Seal	30	300TRQ.V2-30	Overload Spring Dia 7.7mm
3	1000TRQ.V2-03	O-Ring, (Ex: 40.40 In: 34.34 Cs: 3.03)	31	300TRQ.V2-31	Screw
4	1000TRQ.V2-04	Cylinder Head Ass'y	32	DH03.V2-39	O-ring, (Ex: 12.81 In: 9.25 Cs: 1.78)
5	SB-6.0	Steel Ball 6.0mm	33	300TRQ.V2-33	Screw
6	300TRQ.V2-06	O-Ring, (Ex: 15.35 In: 10.59 Cs: 2.38)	34	300TRQ.V2-34	Quick Lift Spring Dia 7.6mm
7	300TRQ.V2-07	Release rod	35	300TRQ.V2-35	Taper valve
8	300TRQ.V2-08	Bush	36	1000TRQ.V2-36	Leg
9	300TRQ.V2-09	Spring Dia 26.5mm	37	1000TRQ.V2-37	Nut (dome)
10	300TRQ.V2-10	Release Knob	38	SWM12.S	Spring Washer M12 Zinc
11	GSM58.S	Grub Screw M5x8 (Single)	39	1500TR.45	Wheel, swivel castor, single bolt (D:88 W:3
12	300TRQ.V2-12	Spring Pin M4 X 24			H:170)
13	RE91/10.02	O-Ring, (Ex: 54.28 In: 47.22 Cs: 3.53)	40	HHB10120.S	Hex Head Bolt M10 x 120mm
14	1000TRQ.V2-14	O-Ring, (Ex: 75.42 In: 69.20 Cs: 3.11)	41	SWM10.SB	Spring Washer M10 Black
15	1000TRQ.V2-15	Oil Filler Plug	42	SN10.S	Steel Nut M10 Zinc
16	1000TRQ.V2-16	Oil Reservoir	43	SS1020.S	Hex Head Set Screw M10 X 20 Zinc
17	1000TRQ.V2-17	Cylinder	44	300TRQ.V2-44	Linkage Stand
18	1000TRQ.V2-18	Piston Rod	45	SWM8.SB	Spring Washer M8 Black
19	1000TRQ.V2-19	Piston Screw	46	SCB825.S	Socket Cap Bolt M8 x 25
20	1000TRQ.V2-20	Steel Seal	47	300TRQ.V2-47	Pedal bearing bush
21	1000TRQ.V2-21	Steel Ball (bigger)	48	300TRQ.V2-48	Pin
22	SM353CEV2.048	Ext Circlip 18.4mm ID	49	300TRQ.V2-49	Pump pedal
23	RW1656.S	Repair Washer M16 X 56 Zinc	50	300TRQ.V2-50	R-Clip 4.3 X 1.4mm
24	300TRQ.V2-24	Bush	51	300TRQ.V2-51	O-ring, (Ex: 18.32 In: 13.62 Cs: 2.35)
25	300TRQ.V2-25	Spring Dia 60mm	52	1000TRQ.V2-52	Pump base
26	300TRQ.V2-26	Pump cylinder	53	300TRQ.V2-53	U cup seal (un30 38 7)
27	300TRQ.V2-27	Outer pump piston	54	300TRQ.V2-54	O-ring, (Ex: 35.92 In: 29.58 Cs: 3.17)
28	300TRQ.V2-28	O-ring, (Ex: 20.22 In: 15.56 Cs: 2.33)	55	300TRQ.V2-55	O-ring, (Ex: 46.32 In: 40.22 Cs: 3.05)

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information.

IMPORTANT: No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

01284 703534

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR 1.

sales@sealey.co.uk

01284 757500 www.sealey.co.uk

1000TRQ Issue 4 PL 11/10/19