



Junction boxes, COMBI 308



COMBI 308



**Protection class:** IP 66  
**Glow wire test:** 750 °C  
**Temperature range:** -30 °C - 100 °C  
**Installation temperature:** -5 °C - 60 °C  
**Voltage:** 400 V  
**Terminals/poles:** 4 mm<sup>2</sup>  
**Advice:** Colour: RAL 7035 · .../S = RAL 9005 · .../W = RAL 9001 · .../DR = RAL 7035 / RAL 3000 · ...  
**Material:** Polypropylene, Gasket: TPE

Type	WISKA-No.	 (mm)		LxBxH external (mm)	
COMBI 308/empty	10060400	3 · 12		85 x 85 x 51	5
COMBI 308/empty/S	10060581	3 · 12		85 x 85 x 51	5
COMBI 308/empty/W	10060610	3 · 12		85 x 85 x 51	5
COMBI 308/empty/DR	10060480	3 · 12		85 x 85 x 51	5
COMBI 308/5	10060401	3 · 12		85 x 85 x 51	5
COMBI 308/5/S	10060580	3 · 12		85 x 85 x 51	5
COMBI 308/5/W	10060611	3 · 12		85 x 85 x 51	5
DIN RAIL KIT 308/108	10060362	-	-	-	1

POLYAMIDE ACCESSORIES  
 MEMBRANE  
 BRASS ACCESSORIES  
 MARITIME  
 STAINLESS STEEL  
 EMC  
 EX E / I  
 EX D  
 VENTING  
 BS 6121  
 SEALINGS, TOOLS  
 JUNCTION BOXES  
 TECHNIQS  
 INDEX