

Product information

98 01 24

- Cranked
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

Box Wrench

IEC 60900 DIN EN 60900




⚡ 1000 V Ⓞ

General

| | |
|-----------------|------------------------|
| Article No. | 98 01 24 |
| EAN | 4003773020318 |
| Weight | 415 g |
| Dimensions | 42 x 40 mm |
| Standard | DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|-----------------------|--------|
| Width across flats S | 24 mm |
| Length l max. | 265 mm |
| Head thickness a max. | 16 mm |
| Depth of crank h max. | 30 mm |
| Head width b max. mm | 38 mm |



technical change and errors excepted

