

Electronic depth callipers

IP67 with integrated EWRI wireless transmission, incl. 3 replaceable gauge slides



Application:

For universal measurement of depth, width, steps and distance dimensions.

Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Auto off
- ABS function
- Preset function

Advantage:

- Key lock to prevent unintentional adjustment
- Switched on automatically by moving the slider
- Unrestricted freedom of movement (radio range up to 6 m)

Delivery:

In a case with battery (1 x 3 V lithium type CR 2032)



Art. no.	31285 512
Brand	MAHR
Manufacturer Part Number	4126532
Min./max. length measuring range	0-100 mm
Data transmission type	MarConnect
Digit increment	0.01 mm
Error limit	0.03 mm
IP protection class	IP 67
Bridge length x bridge width	85 x 8 mm
Type of locating	With locking screw
Calibration Group	B
Number of rechargeable batteries/batteries	1 PCS
Display	Digital
Battery designation	3V CR2032 Lithium
ISO	13385-2
Bridge length	85 mm
Gross Weight	0.600 kg
Product Group	305

EAN

4059192057312