

BLK 2.0 E 350-W sheet metal nibbler, well suited to template cutting



Art. no.	70375 510
Model	BLK 2 E
Manufacturer Article Number	72324060000
Max. cutting capacity in sheet metal (400 N/mm²)	2 mm
Max. cutting capacity in sheet metal (600N/mm²)	1.5 mm
Max. cutting capacity in sheet metal (800N/mm²)	1 mm
Max. cutting capacity in aluminium sheet (250 N/mm²)	2.5 mm
Max. cutting capacity in plastic	2.5 mm
Cutting speed	1 mm/min
Cutting lane width	8 mm
Immersion diameter	18 mm
Min. radius	4 mm
Power input	350 W
Power output	210 W
Stroke rate	1000 rpm
Weight	1.8 kg
Cable length	5 m
Included in delivery	1 BLK 2 E, 1 die, 1 stamp



EAN-Code

4014586869995