

Pneumatic torque screwdriver RRI-SD305 1

Straight version - with shut-off



Application:

Developed for the assembly industry

Execution:

- straight version
- Ergonomic handle with push-to-start function
- Left and right rotation
- Wide torque range

Advantage:

- High torque, very accurate and low vibration
- Easy to adjust
- Shut-off coupling combines low reaction forces with high repeat accuracy



Art. no.	75066 387
Brand	RED ROOSTER
Manufacturer Part Number	RRI-SD30512
Model	RRI-SD30512
Type	Straight version
Suitable for screw	M6
Min. tightening torque	4 Nm
Max. tightening torque	11 Nm
Min./max. tightening torque	4.0-11 Nm
Max. idle speed	500 rpm
Max. torque	11 Nm
Air consumption	11 l/s
Tool holding device	1/4-inch hexagon socket
Connection thread	1/4 inch
Inner hose diameter	6.5 mm
Sound-pressure level	73 dB
Length	290 mm
Weight	0.98 kg
Coupling design	Cut-off clutch
Gross Weight	0.890 kg
Product Group	7AE

EAN

8717981414611