



HAR-FLEX 6P FEMALE IDC CONNECTOR WITH SR

HAR-FLEX 6P FEMALE IDC CONNECTOR WITH SR

WIRING TABLE

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
4	AWG 30	4
5	AWG 30	5
6	AWG 30	6

HARTING P/N	LENGTH ( L )
33152430100382	100±3
33152430200382	200±5
33152430500382	500±5

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY PLASTIC BAG,THEN PUT IT INTO CARTON (QTY ACCORDING TO ACTUAL CONDITION). EXPORT CARTON SHOULD BE STICKED A LABEL WITH P/N AND QTY.

	All rights reserved Department HCS - CN HARTING Customised Solutions D-32339 Espelkamp	All Dimensions in mm Tech. Character. Free size tol. According to production drawing	Created by LINI Lin	Inspected by QINL Qin	Standardisation QINL Qin	Date 2019-08-03	State Final Release
		Title Har-flex 6P,Dul-end,WITH SR,L=xxMM Type TB Number 33 15 243 XXX0382					