


Crimp Fittings

Press-armaturen

Embouts sertis

Raccordi a graffare


Racores para presión



MM

Millimétrique Male
 Außengewindeanschluss 24°, Serie Millimétrique
 Mâle série millimétrique 24°
 Maschio metrico 24° (serie metrica francese)
 Macho fijo de 24°, serie millimétrica

Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G6MM4	1S6MM4	1A6MM4	M12x1,0		6		-4	46,3	22,9		4,2			14
1G8MM4	1S8MM4	1A8MM4	M14x1,5		8		-4	44,5	21,1		4,2			14
1G10MM5	1S10MM5	1A10MM5	M16x1,5		10		-5	47,0	23,1		5,3			17
1G12MM5	1S12MM5	1A12MM5	M18x1,5		12		-5	47,1	23,2		5,3			19
1G12MM6	1S12MM6	1A12MM6	M18x1,5		12		-6	49,0	23,7		6,7			19
1G14MM6	1S14MM6	1A14MM6	M20x1,5		14		-6	49,4	24,1		6,7			22
1G15MM8	1S15MM8	1A15MM8	M22x1,5		15		-8	56,0	26,3		9,6			24
1G16MM8	1S16MM8	1A16MM8	M24x1,5		16		-8	58,0	28,3		9,6			27
1G18MM10	1S18MM10	1A18MM10	M27x1,5		18		-10	58,9	29,5		12,7			30
1G22MM12	1S22MM12	1A22MM12	M30x1,5		22		-12	60,1	29,9		15,5			32
1G25MM12	1S25MM12	1A25MM12	M33x1,5		25		-12	60,1	29,9		15,5			36



GM

Millimétrique Globeseal Female Swivel
 Dichtkopf 24°, Serie Millimétrique
 Globeseal série millimétrique
 Femmina metrica girevole 24° (serie metrica francese)
 Hembra loca de 24° con junta esférica, serie millimétrica

Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G6GM4	1S6GM4		M12x1,0		6	6	-4	49,7	26,3		3,0			17
1G8GM4	1S8GM4	1A8GM4	M14x1,5		8	6	-4	47,0	23,6		4,2			17
1G10GM5	1S10GM5	1A10GM5	M16x1,5		10	8	-5	46,6	22,7		5,3			19
1G12GM5	1S12GM5	1A12GM5	M18x1,5		12	8	-5	46,6	22,7		5,3			22
1G12GM6	1S12GM6	1A12GM6	M18x1,5		12	10	-6	49,1	23,8		6,7			22
1G14GM6	1S14GM6	1A14GM6	M20x1,5		14	10	-6	51,3	26,0		6,7			27
1G15GM8	1S15GM8	1A15GM8	M22x1,5		15	12	-8	55,2	25,5		9,6			27
1G16GM8	1S16GM8	1A16GM8	M24x1,5		16	12	-8	59,2	29,5		9,6			30
		1A18GM10	M27x1,5		18	16	-10	59,1	29,7		12,8			32
1G20GM10	1S20GM10	1A20GM10	M27x1,5		20	16	-10	57,6	28,2		12,8			32
1G22GM12	1S22GM12	1A22GM12	M30x1,5		22	19	-12	58,3	28,1		15,5			36
1G25GM12	1S25GM12	1A25GM12	M33x1,5		25	19	-12	59,3	29,1		15,5			41