


Part-No. 294153-E



MicroCon Male Connector

80-pin, vertical, SMT



Technical Data

Applications	PCB Connectors
Pitch	0.8 mm
Orientation	Vertical
Gender	Male
No. of Pins	80
Termination	SMT
Blindmate	Yes
Class	1
Max Operating Temperature	125 °C
Data Rate	3 Gbit/s
Air- and creepage distance	0.25 mm

Mating Cycles	500
Unmated Stacking Height	2 mm
Contact Plating	Gold plated
Packaging	Tape and reel 630 pcs

Part-No. 294153-E

MicroCon Male Connector

80-pin, vertical, SMT