

M12-Round-Plug Connector, Double-Ended Cordsets,


RST-RKT | RST-RKWT



3-, 4-, 5-, and 8-Poles


Actuator/sensor cordset, double-ended, M12, 3-, 4-, 5- and 8-poles, male straight to female straight connector with self-locking thread and molded cable.

RST-RKT



Actuator/sensor cordset, double-ended, M12, 3-, 4-, 5- and 8-poles, male straight to female 90° connector with self-locking thread and molded cable.


RST-RKWT




Pin Assignments

M12


3 poles




4 poles



5 poles



8 poles



Be Certain with Belden

M12-Round-Plug Connector, Double-Ended Cordsets

Technical Data

Environmental

Degree of protection IP68 / Nema 6P
 Operating temperature range -40°C (-40°F) / +90°C (+194°F)

Mechanical















Housing / Molded body PUR, translucent gray
 Insert PUR orange
 Contact CuZn, gold-plated
 Coupling nut CuZn, nickel-plated
 O-ring FKM

Electrical

Current rating 3-5 poles 4A
 8 poles 1.5A
 Voltage rating 3-4 poles 250V
 5-8 poles 30V

Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Jacket Color	OD
659	PVC	22 AWG	Gray	.190" (4.82 mm)
646	PVC	22 AWG	Gray	.190" (4.82 mm)
647	PVC	22 AWG	Gray	.212" (5.38 mm)
661	PVC	24 AWG	Gray	.232" (5.89 mm)

Part Number	Pins	Standard Cable Lengths	Characteristics
RST 3-RKT 4-3-659/...M	3	0.3M / 0.6M / 1.5M / 1M / 2M / 5M / 10M	 
RST 4-RKT 4-646/...M	4	0.3M / 0.6M / 1.5M / 1M / 2M / 3M / 5M / 6M / 10M / 12M	 
RST 5-RKT 5-647/...M	5	0.3M / 0.6M / 1M / 2M / 5M / 10M	 
RST 8-RKT 8-661/...M	8	0.3M / 0.6M / 1M / 2M / 5M / 10M	 
RST 3-RKWT 4-3-659/...M	3	0.3M / 0.6M / 1.5M / 1M / 2M / 5M / 10M	 
RST 4-RKWT 4-646/...M	4	0.3M / 0.5M / 0.6M / 1.5M / 1M / 2M / 5M / 10M	 
RST 5-RKWT 5-647/...M	5	0.3M / 0.6M / 1M / 2M / 5M / 10M	 
RST 8-RKWT 8-661/...M	8	0.3M / 0.6M / 1M / 2M / 5M / 10M	