

Han A Base Panel 4 Pegs Thermoplastic Co



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 032 0302
Specification	Han A Base Panel 4 Pegs Thermoplastic Co
HARTING eCatalogue	https://b2b.harting.com/09200320302

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With thermo-plastic cover
Type	Low construction

Version

Size	32 A
Locking type	Double locking lever (on the hood)
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
ECHA SCIP number	5b0b428a-c671-4c90-9b6d-16804ea5737a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
California Proposition 65 substances	Nickel
California Proposition 65 substances	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
Requirement set with Hazard Levels	R7 (HL 1-3)

Specifications and approvals

CE	Yes
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	71.94 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140040120
eCl@ss	27440202 Shell for industrial connectors