

Product information

25 01 125

Snipe Nose Side Cutting Pliers (Radio Pliers)

DIN ISO 5745

- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Straight jaws
- Vanadium electric steel, forged, multi stage oil-hardened




General

Article No.	25 01 125
EAN	4003773015932
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	73 g
Dimensions	125 x 56 x 12 mm
Standard	DIN ISO 5745
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 2.2 mm
Cutting capacities hard wire (diameter)	Ø 1.6 mm
Jaw thickness (joint) (T1)	7.0 mm
Tips width (W4)	2.5 mm
Tips thickness (T2)	1.8 mm
Jaw length (L3)	27.0 mm
Head width (W3)	13 mm

Technical details



technical change and errors excepted