

Product information

98 37 3/4"

- For imperial hexagonal head screws
- Basic tool chrome-plated
- With double-hex
- Chrome Vanadium steel

12-Point Socket

With internal square 3/8"

IEC 60900 DIN EN 60900



⚠ 1000 V 

General

| | |
|-----------------|------------------------|
| Article No. | 98 37 3/4" |
| EAN | 4003773020660 |
| Weight | 71 g |
| Dimensions | 49 x 30 x 30 mm |
| Standard | DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|---------------------------------|----------|
| Square drive | 3/8 Inch |
| Ø of effective tool side d max. | 30.0 mm |
| Width across flats S | 3/4 Inch |

technical change and errors excepted