



Sample photo

**Order symbol:** PCT 121210  
**Product nbr:** 7022681  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074003775  
**EI. number:**  
Finland: 3423534  
Denmark: 8212002775  
Italy: 7302035  
Sweden: 7022681  
Norway: 2536610

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		122	120	95	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		4.8	4.7	3.7	Impact Resistance (EN 62262): IK 08/07
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			UV resistance: UL 508
<b>Cover colour:</b>		Clear transparent			Flammability Rating (UL 746 C 5): UL 746C 5V
<b>Cover screws material:</b>		Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>		Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C			Underwriters Laboratories
<b>Continuous:</b>		-40 ... 80 °C			Fimko
<b>Short term:</b>		-40 ... 250 °F			Europe EN 62208: 2003
<b>Continuous:</b>		-40 ... 175 °F			UL Canada
<b>Accessories:</b>					Gost R
TM 1212		Mounting plate			
TRM 0812		DIN-15 Mounting rail			
TRM 1212		DIN-15 Mounting rail			
TRH 1212		DIN-35 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			

