

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190130029**
Status: **Active**
Overview: Standard Quick-Disconnect Terminals
Description: InsulKrimp Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 14-16 AWG, Blue Insulator, Loose in a bag

Documents:

| | |
|--|--|
| 3D Model | Product Specification PS-19902-011-001 (PDF) |
| Drawing (PDF) | Product Specification PS-19902-013-001 (PDF) |
| Product Specification PS-19902-008-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E79133 |

General

| | |
|-------------------------|--|
| Product Family | Quick Disconnects |
| Series | <u>19013</u> |
| Comments | Loose in Bag |
| Crimp Quality Equipment | Yes |
| Insulated | Fully |
| Overview | <u>Standard Quick-Disconnect Terminals</u> |
| Product Name | InsulKrimp |
| Type | Quick Disconnect |
| UPC | 822350963244 |

Physical

| | |
|--------------------------------|-----------------|
| Barrel Type | Closed - Brazed |
| Color - Resin | Blue |
| Flammability | 94V-2 |
| Gender | Female |
| Glow-Wire Capable | No |
| Insulation | Nylon (PA) |
| Lock to Mating Part | No |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 1.256/g |
| Orientation | Straight |
| Packaging Type | Bag |
| Polarized to Mating Part | Yes |
| Tab Thickness | 0.81mm |
| Tab Width | 6.35mm |
| Temperature Range - Operating | 105°C |
| Wire Insulation Diameter | 4.04mm max. |
| Wire Size AWG | 14, 16 |
| Wire Size mm ² | 1.30-2.00 |

Electrical


| | |
|-------------------|---------|
| Voltage - Maximum | 600V AC |
|-------------------|---------|

Material Info

| | |
|--------------------|---------|
| Engineering Number | BB-2318 |
|--------------------|---------|

Reference - Drawing Numbers

| | |
|-----------------------|--|
| Product Specification | PS-19902-008-001, PS-19902-011-001, PS-19902-013-001 |
|-----------------------|--|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19013 Series](#)

This document was generated on 10/12/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION