

Beacon LED XXL

BEACON XXL NB 4K L3 BLK

2093032



Product features

- 2093032 BEACON XXL NB 4K L3 BLK Integrated LED spotlight, black RAL 9005, compact and minimalist design, ideal for double height spaces, retail and display applications, die-cast aluminium body, passive cooling heatsink, beam angle: 21° narrow beam, optics: Fresnel lens for controlled beam, colour temperature: 4000K neutral white, total system power: 48W, total fixture output: 4181lm, luminaire efficacy: 87lm/W, LOR: 100%, colour rendering: Ra 93 typical, LED Chromacity: 3 step MacAdam ellipse, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 1200mA, electronic driver, non-dimmable, switched only, power factor: 0.98 electrical protection: CLASS I, 3-circuit track adaptor, suitable for Concord Lytespan 3 track, ingress protection rating: IP20, suitable for internal environment only, horizontal rotation: 355°, vertical tilt: 90°, lockable positioning using Allen key, dimen...



PRODUCT OVERVIEW

| | |
|-----------------------------|-------------------------|
| Product name | BEACON XXL NB 4K L3 BLK |
| Technology | LED |
| Housing | Aluminium |
| Mount | Track mounting |
| Environment | Internal |
| General application | Retail |
| ETIM Class | EC001744 |
| E-number FI | 4278699 |
| Warranty | 5 years |
| Fixture luminous flux (lm) | 4181 |
| Luminaire efficacy (lm/W) | 87.1 |
| LOR (%) | 100 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 93 |
| Colour Consistency (SDCM) | 3 |
| Beam Angle (°) | 21 |
| Photobiological Risk Group | RG1 |
| Total power consumption (W) | 48 |
| Product Voltage (V) | 240 |
| Electrical protection | Class I |
| Control gear type | Electronic ballast |
| Dimming method | N/A |
| Housing colour | Black |
| IP rating | IP20 |
| Product EAN number | 5025768930326 |

DATA TABLE

General data

| | |
|--------------|-------------------------|
| Product name | BEACON XXL NB 4K L3 BLK |
|--------------|-------------------------|

Beacon LED XXL

BEACON XXL NB 4K L3 BLK
2093032

| | |
|---|----------------|
| Technology | LED |
| Housing | Aluminium |
| Mount | Track mounting |
| Environment | Internal |
| General application | Retail |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC001744 |
| E-number FI | 4278699 |
| Warranty | 5 years |

Optical data

| | |
|----------------------------|---------------|
| Fixture luminous flux (lm) | 4181 |
| Luminaire efficacy (lm/W) | 87.1 |
| LOR (%) | 100 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 93 |
| Colour Consistency (SDCM) | 3 |
| Adjustable chromaticity | N |
| Beam Angle (°) | 21 |
| Photobiological Risk Group | RG1 |

Electrical data

| | |
|--|--------------------|
| Total power consumption (W) | 48 |
| Mains voltage (V) | 220-240V |
| Product Voltage (V) | 240 |
| Lamp power factor | 0.98 |
| Electrical protection | Class I |
| Control gear type | Electronic ballast |
| Transformer required | Yes |
| Dimming method | N/A |
| Drive current (mA) | 1200 |
| Energy Efficiency Class (A->G) of contained light source | E |

Lifetime data

| | |
|------------------|--------|
| Lifespan L70 B50 | 100000 |
| Lifespan L80 B20 | 100000 |
| Lifespan L90 B10 | 55500 |

Physical data

| | |
|-----------------------------|--------------|
| Housing colour | Black |
| IP rating | IP20 |
| Diffuser finish | Diffuse |
| Diffuser material | PMMA Acrylic |
| Reflector finish | None |
| Nominal Product Length (mm) | 85 |
| Nominal Product Width (mm) | 168 |
| Nominal Product Height (mm) | 205 |



Beacon LED XXL BEACON XXL NB 4K L3 BLK 2093032

| | |
|-------------------------------|-------|
| Nominal Product Diameter (mm) | 113 |
| Weight (kg) | 1.375 |

Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5025768930326 |
| Packaging single length / height (cm) | 25.0 |
| Packaging single width (cm) | 19.5 |
| Packaging single depth (cm) | 20.0 |
| DUN14 (outer) | 05025768930326 |
| Units per outer package | 1 |
| Packaging outer length / height (cm) | 25.0 |
| Packaging outer width (cm) | 19.5 |
| Packaging outer depth (cm) | 20.0 |

PHOTOMETRY



TECHNICAL DRAWINGS

