

START eco Flex RGB and RGBW

START ECO FLEX IP67 RGBW

0068124



Product features

- 5 metre IP67 LED reel with pre-attached 3M adhesive type; 24V; RGBW; White colour 2700K



PRODUCT OVERVIEW

Product name	START ECO FLEX IP67 RGBW
Technology	LED
Housing	PVC
Mount	Other
General application	Hospitality, Retail
ETIM Class	EC002706
E-number FI	4276990
Warranty	3 years
Fixture luminous flux (lm)	3250
Luminaire efficacy (lm/W)	45
Colour temperature (K)	2700
CRI (Ra)	50
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	120
Beam Angle (°)	N/A
Photobiological Risk Group	RG1
Total power consumption (W)	72
Electrical protection	Class III
Dimmable	Yes
Dimming method	Other
Housing colour	Transparent
IP rating	IP67
IK rating	IK00
Product EAN number	5410288681245

DATA TABLE

General data

Product name	START ECO FLEX IP67 RGBW
Technology	LED
Housing	PVC
Mount	Other
General application	Hospitality, Retail

START eco Flex RGB and RGBW

START ECO FLEX IP67 RGBW
0068124

Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002706
E-number FI	4276990
Warranty	3 years

Optical data

Fixture luminous flux (lm)	3250
Luminaire efficacy (lm/W)	45
Colour temperature (K)	2700
CRI (Ra)	50
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	120
Beam Angle (°)	N/A
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	72
Mains voltage (V)	24V
Electrical protection	Class III
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Other
Drive current (mA)	3000
Glow Wire Test (°C)	650
Lamp Energy Label (class)	G

Lifetime data

Lifespan L70 B50	30000
Lifespan L70 B10	30000
Lifespan L80 B10	30000
Lifespan L90 B10	30000

Physical data

Housing colour	Transparent
IP rating	IP67
IK rating	IK00
Nominal Product Length (mm)	5000
Nominal Product Width (mm)	14.2
Nominal Product Height (mm)	5.4
Weight (kg)	0.35

Packaging

Single packaging type	Mix(80% carton, 20% plastic)
Product EAN number	5410288681245
Packaging single length / height (cm)	29.5
Packaging single width (cm)	27.5







START eco Flex RGB and RGBW START ECO FLEX IP67 RGBW 0068124

Packaging single depth (cm)	3.0
DUN14 (outer)	15410288681242
Units per outer package	20
Packaging outer length / height (cm)	56.5
Packaging outer width (cm)	32.0
Packaging outer depth (cm)	31.5






Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------


PHOTOMETRY



START eco Flex RGB and RGBW START ECO FLEX IP67 RGBW 0068124



TECHNICAL DRAWINGS




START eco Flex RGB and RGBW
START ECO FLEX IP67 RGBW
0068124



SYLVANIA

0068124



72
kWh/1000h



START eco Flex RGB and RGBW
START ECO FLEX IP67 RGBW
0068124



0068124



72
kWh/1000h

