

Precision pointer

MAHR 1002 precision pointer Millimess



Application:

For measuring lengths. Ideal for measuring instruments and flatness and straightness measurements

Execution:

- Shock resistant
- Ball-guided measuring pin
- Connection for wire lifter
- Pointer fine adjustment
- Adjustable tolerance marks
- Measuring mechanism on ruby bearings

Delivery:

In a case



Art. no.	33163 150
Brand	MAHR
Manufacturer Part Number	4335000
Scale value	0.0005 mm
Length measuring range	0.05 mm
Shank diameter	8 mm
Shaft length	20 mm
Error limit	0.6 µm
With free stroke	Yes
Measurement force	1 N
Reversal error	0.3 µm
Repeat accuracy	0.3 µm
DIN	879
Calibration Group	K
Gross Weight	0.259 kg
Product Group	305

EAN

4059192014261